

Pos.-Nr.	Menge	Einheit	Art.-Nr.	Kurztext	Größe	Hauptlieferant
1	1	Stk.	100282	PCB_20914Tx-01B		
2	5		100021	RESC0402_DNP	DNP	
3	4		100154	CAPC0402_DNP	DNP	
4	2		100169	GRM31C5C2A104JA01	100n	
5	1		100170	CRF0805-FZ-R020ELF	0R02	Farnell GmbH
6	1		100186	NCP15WB473E03RC	NCP15	
7	1		100190	SI7121ADN	SI7121	
8	4		100190	PSMN9R8-30MLC	PSMN9	
9	1		100194	NVR5198NLT1G	NVR51	
10	2		100194	C1206C473J1GEC	47n	
11	12		100204	CC0402KRX7R8BB104	100n	
12	1		100205	CL05C102JB5NNNC	1n0	
13	3		100205	RC0402FR-071KL	1k0	
14	5		100205	RC0402FR-07100KL	100k	
15	2		100205	RC0402FR-0710RL	10R	
16	1		100206	RC0402FR-07220RL	220R	
17	2		100206	RC0402FR-074K7L	4k7	
18	8		100206	RC0402FR-0710KL	10k	
19	1		100208	RC0402FR-0747KL	47k	
20	1		100231	GRM155R71H223KA12D	22n	
21	2		100234	NX138BKW	NX138	
22	1		100237	RC0603FR-10100kL	100k	
23	2		100250	RS1JFA	RS1JF	
24	2		100253	RC0603FR-07390KL	390k	
25	1	Stk.	100272	P9242-R3NDGI	P9242-	
26	3	Stk.	100272	CL10A106MA8NRNC	10u	
27	5	Stk.	100272	GRM155R61E105MA12D	1u	
28	2	Stk.	100272	CL05C560JB51PNC	56p	
29	1	Stk.	100272	GRM155R71E682JA01D	6n8	
30	1	Stk.	100272	LQM18PN4R7MFRL	4u7H	
31	1	Stk.	100272	ACM4520-901-2P-T000		
32	1	Stk.	100272	GRM188R61E475KE11D	4u7	
33	1	Stk.	100272	CL05B681KB5NNNC	680p	
34	2	Stk.	100273	RC0603FR-07200KL	200k	
35	3	Stk.	100273	CGA3E1C0G2A562J080AC	5n6	
36	1	Stk.	100273	RC0402FR-072K4L	2k4	
37	4	Stk.	100273	CL21A226MAYNNNE	22u	
38	4	Stk.	100273	RC0402FR-0712RL	12R	
39	1	Stk.	100273	RC0805FR-073R3L	3R3	
40	1	Stk.	100273	ACM4520-231-2P-T000		
41	1	Stk.	100274	0685T2000-01	2A	
42	1	Stk.	100283	10144041-08011LF		

Hersteller Referenzen Langtext

	PCB	
-	R306,R514,	RESC0402 Footprint,
-	C509,C508,	CAPC0402 Footprint,
Murata	C503,C504,	GRM31C5C2A104JA01
Bourns	R500,	RESC0805 0R020 1%
Murata	R303,	NTC 0402 47k 3%
Vishay	T504,	P-channel -30V,
Nexperia	T501,T500,	N-channel 30V,
onsemi	T400,	N-channel 60V,
Kemet	C506,C505,	C1206C473J1GEC
Yageo	C307,C200,	CC0402KRX7R8BB104
Samsung	C405,	CL05C102JB5NNNC
Yageo	R300,R308,	RESC0402 1K0 1%
Yageo	R506,R504,	RESC0402 100K 1%
Yageo	R502,R501,	RESC0402 10R 1%
Yageo	R516,	RESC0402 220R 1%
Yageo	R309,R310,	RESC0402 4K7 1%
Yageo	R307,R517,	RESC0402 10K 1%
Yageo	R304,	RESC0402 47K 1%
Murata	C400,	GRM155R71H223KA12
Nexperia	T506,T505,	N-Channel 60V, 2.1Ohm
Yageo	R404,	RESC0603 100K 1%
onsemi	D400,D401,	600V/0.8A Fast
Yageo	R406,R407,	RESC0603 390K 1%
Renesas	IC300,	15W Wireless Charging
Samsung	C313,C312,	10 μ F \pm 20% 25V
Murata	C300,C302,	CAP CER 1UF 25V X5R
Samsung	C305,C304,	CAP CER 56PF 50V
Murata	C314,	CAP CER 6800PF 25V
Murata	L300,	FIXED IND 4.7UH
TDK	L200,	2 Line Common Mode
Murata	C203,	GRM188R61E475KE11
Samsung	C401,	CAP CER 680PF 50V
Yageo	R403,R401,	RC0603FR-
TDK	C402,C403,	CAP CER 5600PF 100V
Yageo	R402,	RES 2.4K OHM 1%
Samsung	C513,C501,	MLCC22UF25V 20
Yageo	R507,R508,	RESC0402 12R \leq 1%
Yageo	R520,	RESC0805 3R3 1%
TDK	L500,	2 Line Common Mode
Bel	F200,	2A Surface Mount Slow
Amphenol	CN100,	Socket & Kabelgehäuse